



APPLICATION:

General illumination for health care facilities, educational institutions, airports, commercial offices, retail and many other applications.

PRODUCT FEATURES:

- Twilite Series proprietary "light lock system" prevents light leakage at both ends of lamp shield
- Steel side reflectors intersect with housing to ensure seamless appearance
- Lamp shield pivots down for easy installation of lamps
- Ballast can be accessed from below the ceiling
- Post-painted soft white powder coat finish maximizes distribution and efficiency while providing visual comfort
- Lamp shield is 60% perforated white steel mesh, backed with high-transmission white acrylic diffuser for optimum light efficiency, maximum glare control and lamp image prevention
- All sides and corners are turned in and hemmed, removing sharp edges for safe handling and installation
- Four corner tie points are standard for safety wire support when required
- Built-in earthquake clips standard.

- Same-day shipping on most options (Consult factory)
- Supplied standard with Philips Advance, GE or Universal ballast
- Wide variety of dimming and daylight harvesting options available
- Consult factory for continuous row mounting
- CEE qualified ballast comes standard on most fixture options (Consult factory for details)
- NEC required ballast disconnect is standard

LISTING

UL/C-UL listed to US and Canadian standard

WARRANTY

Guaranteed for one year against mechanical defects

Ordering Information > Example: 24-ODS-2-32-T8-ADV-10-MVOLT

24	ODS								
FIXTURE SIZE 24-2' X 4'	TRIM TYPE (Blank)-Grid (Consult factory for Slot T mounting option)			VOLTAGE² (Blank)- MVOLT (120/277) 120 277 347	# OF BALLAST (Blank) - 1 Ballast 2 - 2 Ballasts	BALLAST FACTOR (Blank)- Normal BF HBF- High BF LBF- Low BF	LAMP INSTALLED (Blank)- No lamp L30K- 3000K L35K- 3500K L41K- 4100K L50K- 5000K		
SERIES ODS-Oracle Side Basket Direct/Indirect	# OF LAMPS/LAMP TYPE								
	2-32-T8 (2 lamps/32W/T8) 4-32-T8 (4-lamps/32W/T8)	2-28-T5 (2 lamps/28W/T5) 4-28-T5 (4-lamps/28W/T5) 2-54-T5HO (2 lamps/54W/T5HO)							
	(For other lamp type, please consult factory)								

BALLAST CONFIGURATION & CODE			
32W/T8	28W/T5	54W/T5HO	DESCRIPTION
(Blank)	-	-	Electronic Instant Start
EPS	(Blank) ¹	(Blank)	Electronic Program Start
ADV-7	-	ADV-7 ¹	Advance Mark-7 ²
ADV-10	-	ADV-10 ¹	Advance Mark-10 ²
-	ADV-OPT	-	Advance Optanium ²
ADV-ESS	-	-	Advance Essential ²
ADV-ROVR	-	ADV-ROVR	Advance Rover ²
LUT-EHD	LUT-EHD ¹	LUT-EHD ¹	Lutron Ecosystem H-Series ²
LUT-2W ¹	-	-	Lutron Tu-Wire ²
LUT-EC3	LUT-EC3 ¹	-	Lutron Ecosystem ²
LUT-EC5	LUT-EC5 ¹	LUT-EC3 ¹	Lutron Eco-10 ²
LUT-TVE ¹	-	-	Lutron Tve ²
LUT-H3D	LUT-H3D ¹	LUT-H3D	Lutron Hi-Lume 3D ²
-	-	LUT-ECO ¹	Lutron Ecosystem (347V Only) ²

1- Requires 2 Ballasts for 3 lamps
2- Voltage must be specified for dimming ballast.

EMERGENCY BATTERY PACK OPTIONS (L. = LUMENS)	
ORDER CODE	DESCRIPTION
EMG-T8-BX-450	Up to 450 L. for T8 or BX
EMG-T8-BX-600	Up to 600 L. for T8 or BX
EMG-T8-BX-700	Up to 700 L. for T8 or BX
EMG-T8-BX-1400	Up to 1400 L. for T8 or BX
EMG-T5-520	Up to 520 L. for T5
EMG-T5-T5HO-700	Up to 700 L. for T5 or T5HO
EMG-T5-T5HO-1300	Up to 1300 L. for T5 or T5HO
EMG-T8-BX-T5-T5HO-3200	Up to 3200 L. for T8, BX, T5 or T5HO
EMG-SD-T8-BX-T5-T5HO-1400	Self-Diagnostic 1400 L. for T8, BX, T5 or T5HO
EMG-ICE-T8-BX-T5-T5HO-1400	ICE Pack 1400 L. for T8, BX, T5 or T5HO
GTD	Generator Transfer Device

MANY OTHER BODINE AND IOTA EMERGENCY PACKS ARE AVAILABLE. PLEASE CONSULT FACTORY. VISIT WWW.BODINE.COM OR WWW.IOTAENGINEERING.COM FOR MORE DETAILS.

OTHER OPTIONS			
24FK	- Flange Kit for 2' X 4' Fixture	SBF	- Internal Slow-Blow Fuse
C3	- 6' 3-wire Flex Cable (Single Circuit)	RIS	- Radio Interference Suppressor
C4	- 6' 4-wire Flex Cable (Double Circuit)	DCR	- Dust Cover
FBF	- Internal Fast Blow Fuse	USA	- Made in America Compliance