

# **Ordering Guide**

MODEL	OPTICS	сст	LUMENS <sup>2</sup>	LENGTH <sup>3</sup>	MOUNTING <sup>4</sup>	FINISH	OPTIONS
ADL-RO4-I	WRA						
ADL-RO4 Indirect	WRA = White Acrylic Ribbed Lens	27 = 2700K 80CRI 30 = 3000K 80CRI 35 = 3500K 80CRI 40 = 4000K 80CRI 50 = 5000K 80CRI 90 CRI add '9' Ex: 940 = 4000K @ 90 CRI BIOS SkyBlue' Spectrally optimized circadian solutions. TUNABLE WHITE (2700K-6500K) 2DIM10 = for 0-10V 2DIM2 = for DMX 2PSQ = for Lutron 2ESN = for Philips	LO = 600/ft (5W/ft, 114LPW) SO = 800/ft (7W/ft, 114LPW) HO = 950/ft (9W/ft, 106LPW) Consult factory for additional lumen packages. All values nominal.	4 = 4 ft 6 = 6 ft 8 = 8 ft For other enter row length (e.g. 48 = 48 ft)	AC = Aircraft Cable PD = Pendant Stem	W = White CC = Custom Color AMW = Anti-Microbial White	DIMMING DRIVERS  DIM10 = 0-10V (1%) - Standard  DIMSR = 0-10V (5.0%) Sensor Ready  DIMST = Step Dimming (40%/100%)  DALI = DALI (5.0%)  LUTRON™ DIMMING DRIVERS  LDE1 = Hi-Lume™ 1% EcoSystem™  L3DA3W = Hi-Lume™ 1% 3-Wire  LTEA2W = Hi-Lume 1% 2-Wire 120V  EMERGENCY  EMC = Emergency Circuit  GTD = Generator Transfer Device  EPC4 = 4W Emergency Battery Pack  EPC7 = 7W Emergency Battery Pack  EPC10 = 10W Emergency Battery Pack  EPC12 = 12W Emergency Battery Pack

<sup>1</sup>BIOS SkyBlue Biological Static & Dynamic page 4.

 $^2$ Delivered Lumens at 80+CRI 3500K CCT. Use the following multiplier to estimate delivered lumens at other CCTs: 2700K = 0.94, 3000K = 0.96, 3500K = 0.98, 5000K = 1.02. See page 3 for photometry.

<sup>3</sup>See page 2 for actual fixture lengths and suspension locations.

<sup>4</sup>See page 3 for mounting details and full specifications.














#### **Individual Fixtures & Continuous Rows**

NOMINAL LENGTH	ACTUAL LENGTH			
4'	4' 1/4"	46 1/2"		
8'	8' 1/4"	94 1/2"		
12'	12' 1/4"	94 1/2"	48"	
16'	16' 1/4"	94 1/2"	96"	
20'	20' 1/4"	94 1/2"	96"	48"
24'	24 1/4"	94 1/2"	96"	96"

Individual fixtures and rows are continuously illuminated and joined with included aligner brackets and hardware. Power feed locations and mounting locations are shown below.

Individual fixtures up to 8' nominal and continuous rows up to 24' nominal are dimensioned as shown below. Continuous rows longer than 8' and patterns, including EPC/EMC and sensor locations must be approved prior to manufacturing.



## **Emergency & Sensor Locations**

EPC will control entire length of individual fixtures. Individual fixtures of differing lengths will deliver the same lumens under EPC power (a 4' fixture will deliver the same total lumens over half the length of an 8' fixture). EMC controlled individual fixtures will deliver lumens per foot as originally specified, unless dimmed at time of power loss. Consult factory for EMC dimming override device.

4' Individual	
8' Individual	For individual fixtures to 8' EPC/EMC will power entire fixture.
24' Row (3x8')	
24' Row (3x8')	For continuous rows longer than 8' one EPC/EMC will be located in the feed section (end-left) of the row as shown below.
24' Row (3x8')	If two EPC/EMC's are required their default locations will be in the feed section (end-left) and last section (end-right) as below.
	Custom placement of one or more EPC/EMC's must be clearly identified during ordering.
8' Individual	SENSORS (Integral) for individual fixtures will control entire length of fixture and will be located on feed end of fixture.
24' Row (3x8')	SENSORS for rows by default will control the feed section (end-left) of the row. Sensors can control more than an 8' section


SENSORS for rows by default will control the feed section (end-left) of the row. Sensors can control more than an 8' section within a row. Consult factory for sensor/section options, or for multiple sensors in a continuous row.



## **Standard Suspension Options**

Standard suspension options include adjustable self-locking aircraft cables (AC) and rigid pendant stems (PD). AC assembly is 48" x 1/16" with a 5" feed canopy and 2" suspension canopies. 60" 18 gauge power and 22 gauge dimming control SJT feed.

PD assemblies are 5/8" dia. (or 3/8" IP) hollow stem for power feed by others, 24" is standard. Consult factory for longer suspension lengths and other mounting options.






PD = Pendant Stem


## **Photometry**

#### ADL-RO4-I-WRA-40-LO-4




4000K CCT WATTS: 21 LUMENS: 2398 LPW: 114 Distribution: 92% Indirect 8% Direct

#### ADL-RO4-I-WRA-40-SO-4



4000K CCT WATTS: 28 LUMENS: 3198 I PW: 114 Distribution: 92% Indirect 8% Direct

#### **Installation Detail**



# **Specifications**

HOUSING: Extruded aluminum housing. Joiner ends are notched for continuous appearance in row-mounted applications. Machined end-caps.

REFLECTOR: Die-formed stee finished in highly reflective baked white enamel.

**OPTICS**: LED optimized white ribed acrylic lens (WRA) is standard.

LED Static white LED modules in 30/35/40 & 50K CCT, 80/90CRI. Lumen maintenance minimum L<sub>70</sub>= 50,000 hours. 3 SDCM color consistency. BIOS SkyBlue and Tunable White options available. Field replaceable.

DRIVER Standard driver is Class 2 AOC 0-10V to 1%, 120/277V input, PF > 90%, THD < 20 @ 120V. Additional dimming protocols available. All drivers prewired from factory for connection to control system (by others). Field replaceable.

MOUNTING Standard options include adjustable self-locking aircraft cables (AC), and rigid pendant stems (PD). AC assembly is 48" x 1/16" with a 5" feed canopy and 2" suspension canopies. 18 gauge power and 22 gauge dimming control SJT feed.

FINISH: Aluminum fixture housing and steel components are finished in baked white enamel applied over a five-stage pretreatment process. Canopies and pendant stems are white enamel unless otherwise specified.

CERTIFICATION: Luminaires are cETLus listed conforming to UL STD. 1598 and certified to CSA STD C22.2 NO. 250.0. Suitable for dry & damp locations. Union Made in the United States of America. I.B.E.W. RoHS compliant.

Day-O-Lite, a division of SCW Corporation. All rights reserved. The Day-O-Lite logo is a registered trademark of SCW Corporation. Day-O-Lite reserves the right to change specifications without notice for product improvement.



700

## **BIOS SkyBlue**

BIOS SkyBlue biological technology brings the benefits of blue skies inside. BIOS SkyBlue is the only spectrally optimized circadian solution to pinpoint the region that drives wellness benefits including: increased alertness, enhanced productivity, better mood, and better sleep. More information may be found at www.bioslighting.com or by contacting Day-O-Lite directly.

## **BIOS Biological Static** - Daytime Solution

BIOS Biological Static solutions are designed for daytime applications. BIOS Static Biological LED features key BIOS SkyBlue™ (490nm) for maximum daytime circadian impact. BIOS Static Biological LED Light Engines are available in 3000K, 3500K, and 4000K. Lighting controls are easy; simply switch the lights on/off or the lights can be dimmed using a single-channel constant current (CC) LED driver with any standard dimming interface.

#### Applications:

- Spaces occupied during the daytime ~7am 7pm
- K-12 Schools / Higher Education
- Offices
- Daytime Adult Care Facilities
- Medical Offices

BIOS Biological Static Ordering Codes:

**B30** = 3000K

**B35** = 3500K

**B40** = 4000K



Wavelength (nm)

BIOS Biological Static 3500K

# BIOS Biological Dynamic - Day & Night Solution A

BIOS Biological Dynamic solutions are designed to transition from daytime to evening in a dim-to-warm protocol. The daytime CCT includes full BIOS SkyBlue™ (490nm) for maximum daytime circadian impact, while the evening spectrum removes BIOS SkyBlue™ altogether, providing a minimal circadian stimulus after hours. Available in 3000K-2700K, 3500K-3000K and 4000K-3500K. Simply dim the lights in the evening to remove the daytime SkyBlue wavelengths (490nm) and convert your lights from day mode to night mode via a single controller (0-10V, ELV, DMX, Wireless).

# BIOS Biological Tunable White - Day & Night Solution B

BIOS Biological Tunable solutions are designed to transition from daytime to evening in a dim-to-warm protocol. The daytime CCT includes full BIOS SkyBlueTM (490nm) for maximum daytime circadian impact, while the evening spectrum removes BIOS SkyBlueTM altogether, providing a minimal circadian stimulus after hours. Available in 3000K-2700K, 3500K-3000K and 4000K-3500K. Simply dim the lights in the evening to remove the daytime SkyBlue wavelengths (490nm) and convert your lights from day mode to night mode via a single controller (0-10V, ELV, DMX, Wireless).

BIOS Biological Tunable is also compatible with two-channel color tuning systems. Simply dim the lights in the evening to convert your lights from day mode to night mode via a multi-channel controller (0-10V, ELV, DMX, Wireless). 3000K, 3500K and 4000K CCTs all dim to 2700K.

#### Applications:

- Spaces occupied overnight (~ 7pm to 7am)
- 24-hour spaces
- Shiftwork & Hospitals
- Senior Living, Alzheimer's Dementia & Assisted Living
- · Higher Education, including student and staff
- Workplace, including areas occupied after 7pm

BIOS Biological
Dynamic White
Ordering Codes:

BIOS Biological
Tunable White
Ordering Codes:

**B30D** = 3000K-2700K **B30T** = 3000K-2700K **B35D** = 3500K-3000K **B35T** = 3500K-2700K **B40D** = 4000K-3500K **B40T** = 4000K-2700K

# BIOS Biological Dynamic 3500K

